

CURRENT PROFILER

Aquadopp Profiler 400 kHz



Up to 90 m current profiling range; ideal for mean current measurements

The Aquadopp Profiler is a highly versatile Acoustic Doppler Current Profiler (ADCP) available in four profiling range options, from < 1 m to > 85 m. Designed for simple yet powerful operation, this current profiler is packed with features used by engineers and researchers to enable accurate and effective hydrodynamic data collection in a variety of environmental conditions.

Aquadopp Profiler 400 kHz



Highlights

- ✓ Up to 90 m current profiling range
- ✓ Ideal for mean current measurements
- ✓ Easy to operate and deploy

Applications

- ✓ Mean flow measurements with high focus on ease of use and simplicity
- ✓ Measurements in flow regimes with strong variations in flow speeds
- ✓ Studies of tidal currents
- ✓ Measurements of combinations of waves and currents
- ✓ Mounted on surface buoys
- ✓ Suitable for wave buoys

Technical specifications

→ Water velocity measurements

Maximum profiling range	60-90 m
Cell size	1-8 m
Minimum blanking	1 m
Maximum number of cells	128
Measurement cell position	N/A
Default position (along beam)	N/A
Velocity range	±10 m/s
Accuracy	±1% of measured value ±0.5 cm/s
Velocity precision	Consult instrument software
Maximum sampling rate (output)	1 Hz
Internal sampling rate	3 Hz

→ Echo intensity (along slanted beams)

Sampling	Same as velocity
Resolution	0.45 dB
Dynamic range	90 dB
Transducer acoustic frequency	400 kHz
Number of beams	3
Beam width	3.7°

→ HR option

Maximum profiling range	N/A
Cell size	N/A
Minimum blanking	N/A
Maximum number of cells	N/A
Range/Velocity limitations	N/A
Accuracy	N/A
Max. sampling rate	N/A

→ Z-Cell option

Cell zero acoustic frequency	N/A
Maximum profiling range	N/A
Number of beams	N/A

→ Sensors

Temperature:	Thermistor embedded in head
Temp. range	-4 to +40 °C

Aquadopp Profiler 400 kHz



→ Sensors

Temp. accuracy/resolution	0.1 °C/0.01 °C
Temp. time response	10 min
Compass:	Magnetometer
Accuracy/resolution	2°/0.1° for tilt < 20°
Tilt:	Liquid level
Accuracy/resolution	0.2°/0.1°
Maximum tilt	30°
Up or Down	Automatic detect
Pressure:	Piezoresistive
Range	0-100 m (inquire for options)
Accuracy/precision	0.5% FS / 0.005% of full scale

→ Analog inputs

No. of channels	2
Supply voltage to analog output devices	Three options selectable through firmware commands: 1) Battery voltage/500 mA, 2) +5 V/250 mA, 3) +12 V/100 mA
Voltage input	0-5 V
Resolution	16-bit A/D

→ Data recording

Capacity	9 MB, can add 4/16 GB
Data record	9*Ncells + 32 bytes
Diagnostics record	N/A
Wave record	Nsamples * 24 + 60 bytes
Mode	Stop when full (default) or wrap mode

→ Real-time clock

Accuracy	±1 min/year
Backup in absence of power	4 weeks

→ Data communications

I/O	RS-232 or RS-422
Communication baud rate	300-115200 Bd
Recorder download baud rate	600/1200 kBd for both RS-232 and RS-422
User control	Handled via "Aquadopp" software, ActiveX@function calls, or direct commands with binary or ASCII data output

→ Connectors

Bulkhead	MCBH-8-FS
Cable	PMCIL-8-MP on 10m polyurethane cable

→ Software

Aquadopp Profiler 400 kHz



Functions Deployment planning, instrument configuration, data retrieval and conversion (for Windows®)

→ Power

DC input	9-15 V DC
Maximum peak current	3 A
Avg. power consumption	0.1 W
Sleep current	< 100 μ A
Transmit power	0.3-20 W, 3 adjustable levels

→ Batteries

Battery capacity	1) 50 Wh (alkaline or Li-ion), 2) 165 Wh (lithium), 3) Single or dual
New battery voltage	13.5 V DC (alkaline)

→ Environmental

Operating temperature	-5 to +40 °C
Storage temperature	-20 to +60 °C
Shock and vibration	IEC 60068-1/IEC60068-2-27/IEC60068-2-64
EMC approval	IEC 61000
Depth rating	300 m

→ Materials

Standard model	POM and polyurethane plastics with titanium fasteners
----------------	---

→ Dimensions

Maximum diameter	117 mm
Maximum length	~600 mm (single battery), +110 mm (double battery) depending on head configuration

→ Weight

Weight in air	3.4 kg
Weight in water	0.2 kg

→ Options

1) Alkaline, lithium or Li-ion external batteries, 2) Inquire for different head configurations